

The Future of Fume Extraction



FEATURES

- Clear & informative graphic display
- Highest grade HEPA and carbon technology
- · Automatic electronic flow control maintains a constant extraction rate even as the filter blocks
- Gas and particle sensors to warn the operator
- Adjustable airflow

SPECIFICATIONS

Voltage	120v	230v
Volume Part Number	0LX4001D	0LX4000D
Vacuum Part Number	080411D	080410D
Wattage	1.2kW	1.2kW
Frequency	50Hz / 60Hz	50Hz / 60Hz
Cabinet Height	710mm	710mm
Cabinet Width	465mm	465mm
Cabinet Depth	528mm	528mm
Cabinet Weight	50kg	50kg
Sound Level	<60dBa	<60dBa
Airflow	400m3/h	400m3/h

INCLUDED AS STANDARD...

FILTERS



Main Filter Code 113505

Description HEPA/Chemical



Pre-filter Code 200025

Description F5 Pad

Find out more:



www.purex.co.uk



purex@purex.co.uk



+44 (0)1405 746030

CONNECTION KIT

Connection kit is included see overleaf for options

OPTIONS

Main Filter

Code:	Description:
113505H	HEPA/Chemical (Hydrophobic)
113579	HEPA/Twin Chemical
113668	HEPA/Twin Chemical
113512	HEPA/Chemical (Cleanroom)
113669	HEPA/Chemical (Cleanroom)
113508	Chemical
113809	HEPA
113513	Solvent Lock


Main Filter


Code:Description:113662Chemical Special113505PChemical Special113531Pleated Bag

Pre-filter

Code: Description: 200524 F8/F9 Pad


Connection Kits








Purex Inlet

Diameter









If you do not see a connection kit that fits your machine or pipework, please contact Purex or your representative

Interfacing



Interfacing can remotely start the Purex machine when the connected machine starts.

Interfacing can also warn the connected machine when the Purex machine is in alarm.

Take a look through our Interfacing Guide to see our extensive range of options



Purex International Limited QWP House, Island Drive Capitol Park, Thorne Doncaster, UK DN8 5UE